



# HIQ THERMAL TRANSFER TAPE & INK RIBBON

Highlights • Soft strong tape • Perfect adhesion • Tape and ribbon: a good match

## Continuous tape

Width: 30, 35, 40, 50, 60, 65, 70, 80 and 90 mm.

Length roll: 50 m.

## Die-cut tape

Size label (w x h):	41 x 16 mm	46 x 19 mm	63 x 12,7 mm
	63 x 19 mm	70 x 38 mm	76 x 25 mm
	80 x 19 mm	80 x 30 mm	90 x 25 mm
	90 x 38 mm	90 x 50 mm	

Length roll: 50 m.

Colours: white, yellow, orange, red, pink, blue, green, high visibility yellow and mint green.

Die-cut tape can be preprinted.

**Ink ribbon** Length: 104 m      Width: various widths

**Colours ink ribbon for wet wash**      Black-red-green-blue

**Colour ink ribbon for dry cleaning**      Black

## HiQ tape and ribbon

HiQ products have been designed for use in the HiQ printers. The soft, strong tapes have been developed to give the adhesion required for the industrial laundry industry on a label that can be printed by thermal transfer printers. The compatibility of the tape and the ribbon are an extremely important part of this system. These supplies have been developed to label any garment, including clean room material.

## The possibilities

HiQ tape is soft and strong and the die cut tape can be preprinted. Continuous HiQ tape can be cut or partially cut into labels by the HiQ-printer. Your logo can be printed on every label, together with personalized text.

HiQ tape is Oeko-Tex certified:



Die-cut (perforated) tape can be separated by hand.

Pre printed tape: the die-cut tape can be pre printed with your logo and/or text in any colour of colour combination you want.

## HiQ-Clean

Another item of the HiQ series is HiQ-Clean. Tape from this range has a different adhesive layer, making it possible to apply the tape to barrier fabrics and similar synthetic materials. This includes specialist workwear in the microelectronics, pharmaceutical and nuclear industries.

HiQ-Clean is also ideally suited for textiles in clean room environments. It is, however, not suitable for surgical clothing which is sterilized using an autoclave.

## A good match

The packaging was designed to keep the tape and ink in sets to ensure product integrity through your washing processes. Each box contains two 50-meter rolls of tape and one 104-meter ink ribbon. The number of labels per roll will, of course, depend on the size of label you choose.

