

## **TEMPERATURE INDICATION LABELS**

The heat is on...

## Highlights • Accurate • Fast • Easy

## Why check the temperature?

For optimal sealing results, the temperature, pressure and time must be set according to the specifications that come with the product to be applied.

When one or more parameters are not set correctly, the label, patch, emblem or transfer will not perform as designed and this will bring unneeded cost.

The Temperature Indicator Labels are available in four ranges:

93	С		3	2	С	
						_

• 143 °C – 182 °C

Example of unused label showing

temperature

Range 1

Range 2

Range 3

Range 4

40 labels per bag.

With both ranges the temperature is showed over eight intervals, this gives a very accurate readout of the actual interplaten temperature.

143

49

154

160

60

166

43

10

## How it works?

166

For optimal results place a temperature indication label with the yellow side upwards on the lower platen of the heat seal press and close the press for 7 seconds.

When a temperature is reached within the range of the labels, depending on the temperature, you will see one or more boxes' color changed to black. The box closest to the actual temperature changes to grey.

> ranging between  $\rightarrow$  149 °C and  $\leftarrow$  154 °C

Temperature ranging between  $\rightarrow$  204 °C and  $\leftarrow$  210 °C